

DTE[®]

D600

Ultrasonic Scaler

Pleasant & Efficient



Intelligent power output
Experience painless treatment

D600 Ultrasonic Scaler

18 invention patents 116 national patents
28 years of research on ultrasonic scaling

HIGH QUALITY HANDPIECE

Shell of the handpiece is made of special imported plastic from America,

which can be autoclaved under high temperature and pressure without cracking or deformation.

Latest handpiece sealing technique, reliable and durable.


Ergonomics design, more comfortable in use.

SINE-WAVE DRIVE

Sine wave drive
Avoiding stimulation caused by instantaneous current output; ensuring comfortable treatment.

Embody comfortable scaling

D600 mild sine wave power output



Rectangular power output of other brand scaler



standard configuration tips

PD1 PD3 PD4 ED1 ED6 ED4 ED5 GD30 PD3D PD4D

high configuration tips (Equipped with two of each tip below)

PD1 PD3 PD4 ED1 ED6 ED4 ED5 GD30 PD3D PD4D



SMART TOUCH SYSTEM

Ultra-sensitive
Waterproof design



AUTOMATIC WATER SUPPLY SYSTEM

Easy to change water,
Increase work efficiency,
Hydrogen peroxide, sodium hypochlorite,
and chlorhexidine is available,
Clear 50ml scale mark makes it
convenient for formulating liquid.




DETACHABLE HANDPIECE WITH LIGHT

Better visibility
Handpiece adopts latest sealing technique
Patients feel more comfortable while scaling



Clear vision
D600 LED with light



Blurred vision
Without light

Supragingival scaling



Implant maintenance



PD90
种植体维护
清洁种植体和修复体

Subgingival scaling



Root canal treatment

Endo scaling



For removing the calcification and bad fillings in root canal



For removing the calcification in the coronal third of the root canal



Root canal retreatment, removing foreign body



Looking for root canal orifice



ED6 ED7
Special material (ED6, ED7) extremely thin and soft, good conductivity to ultrasound

ED6
For removing foreign body in 1/3 deep root canal




ED7
For removing foreign body in 1/3 root canal

ED14
For removing foreign body and broken instruments in root canal (stainless steel)

ED15
For removing root canal fillings and broken instruments (stainless steel)

ED12D
Diamond-coated, ball head, for looking for root canal orifice with security, accuracy and efficiency

Cavity preparation



GD30
For the preparation between pits and fissures

GD31
For the preparation of mesioclusion cavity

GD32
For the preparation of distal mesial cavity

GD30


GD31

GD32

GUILIN WOODPECKER MEDICAL INSTRUMENT CO., LTD.

Registration Add & Manufacturing Add:
Information Industrial Park, Guilin National High-Tech
Information Park 541004 Guilin, Guangxi China
Tel:
Europe Sales Dept.: +86-773-5873196, +86-773-2125222
North America, South America &
Oceania Sales Dept.: +86-773-5873198, +86-773-2125123
Asia & Africa Sales Dept.: +86-773-5855350, +86-773-2125896
Fax: +86-773-5822450
E-mail: woodpecker@glwoodpecker.com, sales@glwoodpecker.com
Website: http://www.glwoodpecker.com

Distributor:



Scan and Login website
for more information

